

PRODUCT DESCRIPTION

BF SUBLISTOP was created to be applied on garments printed with dye sublimation. It comes with a built-in barrier to prevent the migration of pigments, keeping the material's original color unaltered even after multiple wash cycles.

This product is easy to work with; the sticky polyester carrier allows for fast weeding and easy repositioning of details that might have accidentally been removed. It is also soft and comfortable to wear, even with bulky designs.

Because of its 120 micron thickness, BF SUBLISTOP is soft on any fabric.

APPLICATION TECHNIQUES

- Knockout
- Layering from other series

APPLICATION STEPS

- Cut - 45° blade
- Weed excess material
- Turn on your heat press - heat to 140°C/285°F
- Place your graphic on the garment
- Press it - 140°C/285°F for 10 seconds
- Remove the liner - hot

SIZES

H 50 cm L 25 mt / 12,5 mt / 5 mt / 1 mt

H 75 cm L 25 mt (upon request)

H 100 cm L 25 mt (upon request)

H 150 cm L 25 mt (upon request)

Comply with
regulation **REACH**
n°1907/2006/EU

SAFETY NOTICE

The values reported in this document are average values as tested under normal conditions in our lab. We cannot provide a guarantee regarding the information abovementioned in this page. Due to possible variations in the production of garments, B-FLEX recommends testing the material prior to all applications.

TECHNICAL DATA



Film: PU/polyurethane



Thickness: 120μ (±5%)



Liner: adhesive PET



Finish: opaque

PLOTTER SETTING



Cut settings: mirror



Blade: 45°



Minimum cut: 0,5 cm

APPLICATION



Temperature: 140°C - 285°F



Time: 10''



Liner removal: hot



Pressure: medium - 3,5 bar - 50 PSI



Textile: synthetic, sublimated fabrics

WASH RESISTANCE

First wash after application

wait 12 hours

Max wash temperature

40°C - 104°F

Dry clean

✗

Dryer

✗

BF SUBLISTOP

COLOUR GUIDE



- Prevents the color's pigments migration from the fabric to the film's surface
- Fully opaque
- Neon colors available



BF 700ASU
WHITE SUBLISTOP



BF 728ASU
LEMON YELLOW SUBLISTOP



BF 720ASU
MEDIUM YELLOW SUBLISTOP



BF 734ASU
ORANGE SUBLISTOP



BF 730ASU
RED SUBLISTOP



BF 792ASU
GOLD SUBLISTOP



BF 796ASU
SILVER SUBLISTOP



BF FLU020ASU
NEON YELLOW SUBLISTOP



BF FLU030ASU
NEON ORANGE SUBLISTOP



BF FLU040ASU
NEON PINK SUBLISTOP



BF FLU050ASU
NEON GREEN SUBLISTOP

